

625 HF Series High Flow Cartridges

All elements are 5 layer construction for maximum pleat support and dirt loading.



- AMBF offers the highest grade, **90% and 99.98% efficient elements** on the market today
- Our media is **manufactured in-house** under strict guidelines to ensure consistency and maximum dirt loading
- **In-house lamination and calendaring** of our medias allow us to control the final media grades
- Complete in-house testing with a Capillary Flow Porometer guarantees a **superior and consistent product**
- With 8 micron ratings and multiple lengths and 4 end cap configuration to ensure we **produce the element you require**
- Elements have thermally bonded end caps and ultrasonic welded media seams for a **one piece construction**
- Final, one piece construction up to 40" long **ensures zero bypass**
- We install the maximum amount of media in each filter without pleat binding for **increased dirt loading capacity**
- Elements are **100% polypropylene**—media, inner and outer supports mesh and end caps
- Elements meet **FDA Title 21** regulations for food and water contact
- Cartridges are constructed in a **clean room environment**
- Cartridges may be ordered as final **rinsed with 18 mega ohm water**
- We offer **inside out OR outside in** flow pattern for your specific housing application.
- Longer service life equals reduced maintenance and downtime

***Please call with all of your applications
(219) 866-3500***

Materials of Construction		Dimensions (nominal)	
Filter Media:	Polypropylene Melt Blown	Outside Diameter:	6.25"
Core:	Polypropylene	Lengths:	20", 30", 40", 60", & 80"
Netted Outer Cage:	Polypropylene		
Support Material:	Polypropylene		
Sealing:	Thermal Bond		
Gaskets/O-Rings:	Buna N, Viton®, Teflon®, Silicone, Neoprene & EDPM		
Performance Specifications			
Retention Ratings of 90% and 99.98% at: 1, 3, 5, 10, 25, 50 & 100 micron			
Operating Conditions		FDA Listed Materials	
Maximum Differential Pressure: 50 psid @ 180°F, 82°C		Manufactured from materials which are FDA listed for food contact applications in Title 21 of the U.S. code of federal regulations	
Toxicity		Purity	
AMBF's Cartridges are manufactured with no additives or other manufacturing agents. We guarantee all materials used in the production meet FDA Title 21 of the Code of Federal Regulations 174.5 and 177.1520.		Cartridges are Free of Surfactants, Resins, Binders and Adhesives	
Sterilization			
Multiple Autoclaving for 30 Minutes at 250°F (121°C) under no End Load Conditions. In-line Steam Sterilization is not recommended. May be In-line Sanitized with Hot Water at 180°F (82°C) for 1 hour.			

Building a Part Number

625 HIGH FLOW
PLEATED
CARTRIDGE

625	MEDIA	EFFICIENCY	MICRON	CARTRIDGE LENGTH	END CAP	GASKET / O-RING	18 MEGA OHM RINSE
625	E	A	1	5	3	B	R
625	E = Polypropylene	A = 90% B = 99.98%	.5 1 3 5 10 25 50 100	5 = 20 7 = 30 8 = 39 9 = 40 10 = 60 11 = 80 A = custom	4 = 222/Flat 5 = 226/Flat 6 = 225/Flat 9 = Flat/O ring A = Custom	B = Buna V = Viton® T = Teflon® S = Silicone N = Neoprene D = EPDM	R

1030 E. Elm Street Rensselaer, IN 47978
PH (219) 866-3500 FAX (219) 866-3570

Visit **AMBF's website for all of your filtration needs!**
www.AmericanMeltBlown.com

©2012 American Melt Blown & Filtration
Viton and Teflon are registered trademarks of DuPont Dow Elastomers L.L.C. & the DuPont Company

